


### AMRR2D V.2 mRIC R D (P-Receiver)

Hearing loss up to severe-to-profound  
Philharmonie/Symphonie/Concerto/Prelude



#### Fitting range



Key Features	Philharmonie	Symphonie	Concerto	Prelude
Performance	XXXXXX	XXXXX	XXXX	XX
Processing and fine-tuning channels	15	12	10	6
Adaptation manager	•	•	•	•
Fluid Sound Analyser (sound classes)	11 (IE)	7 (IE)	4	3
Programs	5	4	3	3
Smartwind Manager	•			
High-frequency boost	•			
Speech Enhancer	RT/IE	IE		
Digital Pinna	•	•		
HD Locator	•	•	•	
TruSound Softener	•	•	•	
SoundSense Adapt	•	•	•	
Preference Control	•	•	•	•
Soft-level noise reduction	•	•	•	•
Noise reduction	•	•	•	•
ZEN IE	•	•	•	•
Audibility Extender	•	•	•	•
<b>Connectivity</b>				
2.4 GHz control (Android and iOS)	•	•	•	•
2.4 GHz audio streaming (iOS)*	•	•	•	•
<b>Accessories</b>				
DEX assistive listening devices*	•	•	•	•
TONELINK App	•	•	•	•
COM-DEX App	•	•	•	•


\*Compatible with the following: CALL-DEX, TV-DEX, COM-DEX, UNI-DEX, RC-DEX, FM+ DEX, PHONE-DEX

### TECHNICAL DATA


		<b>EAR SIMULATOR</b> IEC 60118-0:1983, + A1:1994	<b>2CC COUPLER</b> IEC 60118-0:2015, ANSI S3.22-2014
OSPL90	1600 Hz Peak Average	131 dB SPL 133 dB SPL 127 dB SPL	122 dB SPL 123 dB SPL 121 dB SPL
Acoustic output (Input 60 dB SPL)	1600 Hz Peak Average	116 dB SPL 119 dB SPL 108 dB SPL	107 dB SPL 109 dB SPL 104 dB SPL
Full-on gain (Input 50 dB SPL)	1600 Hz Peak Average	68 dB SPL 71 dB SPL 69 dB SPL	59 dB SPL 65 dB SPL 60 dB SPL
Acoustic Frequency range		100 Hz - 8050 Hz	100 Hz - 7550 Hz
Harmonic distortion (Typical)	500 Hz 800 Hz 1600 Hz	<2% <2% <2%	<2% <2% <2%
Equivalent input noise		17 dB SPL	20 dB SPL
Battery drain (stand by)		1.27 mA	1.27 mA
Battery drain*		1.43 mA	1.45 mA
Battery life / hours (Type 10 Zn-Air, 100 mAh)*		35 h	35 h
Mobile phone immunity (IEC 60118-13:2016, ANSI C63.19:2011)		IRIL: -25/-28/-10 dB SPL	U-rating: M4

\*Battery life in real-life situations depends among other things on the hearing aid features used, streaming time, and the quality of the battery used.


#### MAXIMUM OUTPUT - EAR SIMULATOR



#### MAXIMUM OUTPUT - 2CC COUPLER



#### OUTPUT - EAR SIMULATOR



#### OUTPUT - 2CC COUPLER

