

GrandAudition RITE with HP-receiver

4 Performance levels




The GrandAudition RITE is based upon the E-Platform with a Sound Class controller that handles automatic processing more accurately and faster than before. The GrandAudition RITE use smart technology that learn from the users' preferences and help guide them to a better, more personalised sound. The RITE has an optional ZPower rechargeable solution.

2.4 GHz Bluetooth connectivity with the customisable App allows for direct streaming of audio as well as direct control from smartphones and tablets.

- Direct wireless mobile connectivity (2.4 GHz)
- Multiple wireless connectivity via Apps and DEX assistive listening devices
- Uses an HP-receiver
- Uses a size 312 battery
- Protection class IP68 (only non-rechargeable solution)
- Moderate to severe-to-profound hearing losses

SUGGESTED FITTING RANGE



STANDARD TECHNOLOGY

- E-platform with with Sound Class Controller
- Improved open-fit rationale
- Acclimatisation rationales
- Power Saver IV technology: Low current consumption


FEATURES	440	330	220	110
Performance	★★★★★	★★★★★	★★★★	★★
Platform	E	E	E	E
SoundSense Adapt	•	•	•	
Adaption manager	•	•	•	•
High-frequency boost	•			
Wind noise reduction	•			
Speech Enhancer RT	RT/IE	IE		
Digital Pinna	•	•		
TruSound Softener	•	•	•	
Soft-level noise reduction	•	•	•	•
Noise Reduction	•	•	•	•
Sound Class Technology 2	11 (IE)	7 (IE)	4	3
HD Locator	•	•	•	
Programs	5	4	3	3
ZEN IE	•	•	•	•
Audibility Extender	•	•	•	•
Preference Control	•	•	•	•
Programmable Push Button*	•	•	•	•
Telecoil	•	•	•	•
ACCESSORIES	440	330	220	110
EVOKE App with SoundSense Learn	•	•	•	
EVOKE App	•	•	•	•
TONELINK App	•	•	•	•
COM-DEX App	•	•	•	•
DEX assistive listening devices**	•	•	•	•
Multiple earware options	•	•	•	•

*Programmable: Preference Control, program shift or a combination of the two
 **Also includes DEX assistive listening devices: CALL-DEX, TV-DEX, COM-DEX, UNI-DEX, RC-DEX, FM+ DEX, PHONE-DEX




*GrandAudition RITE, direct streaming, is compatible with the following devices: iPhone X, iPhone 8, iPhone 8 Plus, iPhone 7, iPhone 7 Plus, iPhone 6, iPhone 6Plus, iPhone 6S, iPhone 6SPlus, iPhone 5S and iPhone SE using iOS 10 or later. Apple, the Apple logo, iPhone, iPad and iPod touch are trademarks of Apple Inc., registered in the US and other countries.


MAXIMUM OUTPUT - EAR SIMULATOR
IEC 60118-0




MAXIMUM OUTPUT - 2CC COUPLER
IEC 60118-7 / ANSI S3.22-2009



OUTPUT - EAR SIMULATOR
IEC 60118-0



OUTPUT - 2CC COUPLER
IEC 60118-7 / ANSI S3.22-2009



Technical data Typical data obtained through standard pure tone measurements. Hearing aid set to Compass Reference Test Gain, unless stated otherwise. Measured using a standard ITE coupler without wax guard. For further information, please contact GrandAudition.

		EAR SIMULATOR IEC 60118-0:1983 + A1:1994	2CC COUPLER IEC 60118-0:2015 / ANSI S3.22-2014
OSPL90	1600 Hz Peak Average	130 dB SPL 138 dB SPL 133 dB SPL	120 dB SPL 133 dB SPL 126 dB SPL
Acoustic output (Input 60 dB SPL)	1600 Hz Peak Average	115 dB SPL 121 dB SPL 113 dB SPL	105 dB SPL 112 dB SPL 109 dB SPL
Full-on gain (Input 50 dB SPL, Compass Full-on gain)	1600 Hz Peak Average	76 dB 84 dB 75 dB	67 dB 74 dB 70 dB
Telecoil output (Input 31.6 mA/m)	1600 Hz Peak Average	115 dB SPL 121 dB SPL 113 dB SPL	105 dB SPL 112 dB SPL 109 dB SPL
Acoustic frequency range		100 Hz - 7300 Hz	100 Hz - 5800 Hz
Harmonic distortion (typical)	500 Hz 800 Hz 1600 Hz	<2% <2% <2%	<2% <2% <2%
Equivalent input noise		21 dB SPL	20 dB SPL
Battery drain (stand by)		1.03 mA	1.03 mA
Battery drain*		1.10 mA	1.14 mA
Battery life / hours (Type 312 Zn-Air, 170 mAh)* (Type 312 rechargeable, 40 mAh)		155 h 35 h	150 h 35 h
Mobile phone immunity (IEC 60118-13:2016, ANSI C63.19:2011)		IRIL: -18/-21/-13 dB SPL	U-rating: M4/T4

*Battery life in real-life situations depends among other things on the hearing aid features used, streaming time, and the quality of the battery used.